

OTM 1

The OTM-1 (Open Tray Monitor) has been designed for the detection and measurement of gamma radiation on potentially exposed tools and objects. There are two models depending on whether the equipment is open on both sides (v.1) or only on the front (v.2).

SPECIFICATION

- 2 plastic scintillation detectors
- Efficiencies: >30% (Co-60), >15% (Cs-137), >6% (Ba-133)
- Lead shielding of 20 mm
- Temperature: 0°C - 50°C
- Humidity max: 90% noncond
- Software 100% customizable



PAGES

[Who we are?](#)
[Distribution](#)
[Software](#)

SECURITY AND PRIVACY

[Legal Notice & Privacy Policy](#)
[Cookies policy](#)



CONTACT

916 466 267
direccion@helgeson.es
 Calle Valdemorillo, 50 28925 Alcorcón, Madrid

Fondo Europeo de Desarrollo Regional

Una Manera de hacer Europa

Helgeson Scientific Services en el marco del Programa IDEX Next

ha contado con el apoyo de ICEX

y con la cofinanciación del fondo europeo FEDER.

La finalidad de este apoyo es contribuir

al desarrollo internacional de la empresa y de su entorno